

FLK 50/EZ-DR/ 100/KONFEK

Order No.: 2289078



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2289078>

Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

| Commercial data | |
|--------------------------|--------------------|
| EAN | 4017918057466 |
| Pack | 1 pcs. |
| Customs tariff | 85444290 |
| Weight/Piece | 0.1732 KG |
| Catalog page information | Page 262 (IF-2009) |

Product notes

WEEE/RoHS-compliant since:
04/04/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

| General | |
|---|----------------------|
| Nominal voltage U_N | < 50 V AC 60 V DC |
| Max. current carrying capacity per path | 1 A |
| Max. conductor resistance | 0.16 Ω /m |
| Ambient temperature (operation) | -20 °C ... 50 °C |

| | |
|---|---|
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Number of positions | 50 |
| Number of positions, control side | 50 |
| Number of connectors, control side | 1 |
| Number of positions, module side | 50 |
| Number of connectors, modul side | 1 |
| Fixed cable length | 1 m |
| Single wire, cross section | 0.14 mm ² |
| AWG | 26 |
| Conductor construction: Number of litz wires: | 7 |
| Single wire, material | Cu tin-plated |
| External diameter | 10.3 mm |
| Cable, preassembly | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding | no |
| Width | 73.9 mm |
| Length | 40 mm |

Certificates / Approvals



Certification

CUL, GOST, UL

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;