

CABLE-FLK50/OE/0,14/ 50

Order No.: 2305871



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2305871>

Round cable assembled with a 50-pos. socket strip and an open end. On the open end, the wires are labeled with 1 to 50 and have ferrules, cable length: 0.5 m

Commercial data	
EAN	4046356039208
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.1119 KG
Catalog page information	Page 261 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
05/02/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General	
Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions	50
Number of positions, control side	50
Number of connectors, control side	0
Number of positions, module side	50
Number of connectors, modul side	1
Fixed cable length	0.5 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
Test voltage	0.8 kV
External diameter	10.3 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Certificates / Approvals

Certifications applied for: UL / CUL

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;