

IBS RBC METER-T

Order No.: 2806286

The illustration shows the versions standard, highly flexible and remote bus cables for underground runs



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2806286>

Remote bus cable, by the meter, for fixed routing

Commercial data

GTIN (EAN)	4017918074791
Note	Made-to-order
sales group	K900
Pack	1 m
Customs tariff	85444993
Weight/Piece	0.07016 KG
Catalog page information	Page 417 (AX-2009)

Product notes

WEEE/RoHS-compliant since:
03/30/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

External sheath

Outer sheath, material	Special mixture on PVC base
External sheath, color	Green RAL 6017
External diameter	7.2 mm

Single wire

Individual wires per module	6
Single wire, color	Color-coded DIN 47100
Structural data	7-strand Litz wires

Mechanical properties

Smallest bending radius, fixed installation	8 x 7.2 mm
Ambient temperature (storage/transport)	-30 °C ... 70 °C

Certificates / Approvals



Certification GOST

Accessories

Item	Designation	Description
------	-------------	-------------

Literature

2743792	IBS SYS PRO INST UM	User Manual, German, for project planning and installation of the INTERBUS system, with collection of data sheets
2743802	IBS SYS PRO INST UM E	User Manual, English, for project planning and installation of the INTERBUS system, with collection of data sheets

Address

PHOENIX CONTACT K.K.
Yusen Shinyokohama 1-chome Bldg. 6F
J-Yokohama 222-0033, Japan
Phone +81/45/471-0030
Fax +81/45/471-0031
<http://www.phoenixcontact.co.jp>



© 2010 Phoenix Contact
Technical modifications reserved;