

RAD-ISM-2400-ANT-OMNI-2-1

Order No.: 2867461

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867461>

Omni-directional antenna, IP65 degree of protection, linear vertical, 2 dBi gain, cable length 1.5 m, MCX (male) connection, impedance 50 Ω , apex angle h/v 360°/75°

Commercial data

EAN	4017918952761
Pack	1 pcs.
Customs tariff	85177019
Weight/Piece	0.0835 KG
Catalog page information	Page 547 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
01/18/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Frequency range	2.4 GHz
Horizontal beamwidth	360 °
Vertical beamwidth	75 °
Impedance	50 Ω

Gain	2 dBi
Type of connection	MCX (male) with cable (1.5 m)
Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-30 °C ... 75 °C
Width	7.8 mm
Height	82.5 mm

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;