

PLC-BSP-120UC/21

Order No.: 2967167



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2967167>

6.2 mm PLC basic terminal blocks with spring-cage connection method, input voltage 120 V AC/DC (without relay or optocoupler)

Commercial data	
GTIN (EAN)	4017918165307
Note	Made-to-order
sales group	G201
Pack	10 pcs.
Customs tariff	85364900
Weight/Piece	0.02747 KG

Product notes

WEEE/RoHS-compliant since:
04/18/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Input data	
Nominal input voltage U_N	120 V AC/DC
Status display	LED
Protective circuitry	Bridge rectifier

Output data

Compatible components	Miniature relay, REL-MR-60DC/21AU, REL-MR-60DC/21; miniature optocoupler, OPT-60DC/48DC/100, OPT-60DC/24DC/2, OPT-60DC/230AC/1
-----------------------	--

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Type of connection	Spring-cage connection
Stripping length	8 mm

General data

Width	6.2 mm
Height	94 mm
Depth	80 mm
Color	green
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Operating mode	100% operating factor
Inflammability class acc. to UL 94	V0
Mounting position	Any
Assembly instructions	In rows with zero spacing

Certificates / Approvals



Certification

CUL, CUL Listed, GL, GOST, UL, UL Listed

Address

PHOENIX CONTACT K.K.
Yusen Shinyokohama 1-chome Bldg. 6F
J-Yokohama 222-0033, Japan
Phone +81/45/471-0030
Fax +81/45/471-0031
<http://www.phoenixcontact.co.jp>



© 2010 Phoenix Contact
Technical modifications reserved;