


PR1-BSP3/2X21

Order No.: 2833534



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2833534>

Relay socket PR1..., for miniature power relay or miniature switching relay with 1 or 2 PDT or solid-state relay of same construction, 1/3 level design, spring-cage connections, connection facility for input/interference suppression modules

Commercial data	
EAN	4017918933784
Pack	10 pcs.
Customs tariff	85366990
Weight/Piece	0.04561 KG
Catalog page information	Page 53 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
12/01/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Certificates / Approvals



Certification

CUL, UL

Accessories		
Item	Designation	Description
Bridges		
2820916	DB 50- 90 BK	Wire bridge, Color: black
2821180	DB 50- 90 BU	Wire bridge, Color: blue
2820929	DB 50- 90 GY	Wire bridge, Color: gray
General		
2833547	EL1-P16	Relay retaining bracket, with eject function and integrated equipment marking area (7.5 x 15 mm), to suit relay socket PR1, for 16 mm high miniature power relay and solid-state relay
2833550	EL1-P25	Relay retaining bracket, with eject function and integrated equipment marking area (7.5 x 15 mm), to suit relay socket PR1, for 25 mm high miniature switching relay and solid-state relay
2833686	LDM- 12- 24DC	Plug-in module, for mounting on PR1 and PR2, with damping diode and yellow LED, polarity: A1- , A2+ (Japan standard), input voltage: 12 -24 V DC \pm 20%
2833699	LDM- 48- 60DC	Plug-in module, for mounting on PR1 and PR2, with damping diode and yellow LED, polarity: A1- , A2+ (Japan standard), input voltage: 48 -60 V DC \pm 20%
2833709	LDM-110DC	Plug-in module, for mounting on PR1 and PR2, with damping diode and yellow LED, polarity: A1- , A2+ (Japan standard), input voltage: 110 V DC \pm 20%
2833657	LDP- 12- 24DC	Plug-in module, for mounting on PR1 and PR2, with damping diode and yellow LED, polarity: A1+ , A2- , input voltage: 12 -24 V DC \pm 20%
2833660	LDP- 48- 60DC	Plug-in module, for mounting on PR1 and PR2, with damping diode and yellow LED, polarity: A1+ , A2- , input voltage: 48 -60 V DC \pm 20%
2833673	LDP-110DC	Plug-in module, for mounting on PR1 and PR2, with damping diode and yellow LED, polarity: A1+ , A2- , input voltage: 110 V DC \pm 20%
2833712	LV- 12- 24UC	Plug-in module, for mounting on PR1 and PR2, with varistor and yellow LED, input voltage: 12 - 24 V AC/DC \pm 20%
2833725	LV- 48- 60UC	Plug-in module, for mounting on PR1 and PR2, with varistor and yellow LED, input voltage: 48-60 V AC/DC \pm 20%
2833738	LV-120-230AC/110DC	Plug-in module, for mounting on PR1 and PR2, with varistor and yellow LED, input voltage: 120 - 230 V AC/110 V DC \pm 20%
2833631	MP 1	Equipment marker, labeling surface 6 x 15 mm
2833741	RC- 12- 24UC	Plug-in module, for mounting on PR1 and PR2, with RC element, input voltage: 12 - 24 V AC/DC \pm 20%
2833754	RC- 48- 60UC	Plug-in module, for mounting on PR1 and PR2, with RC element, input voltage: 48-60 V AC/DC \pm 20%

2833767	RC-120-230UC	Plug-in module, for mounting on PR1 and PR2, with RC element, input voltage: 120 - 230 V AC/DC \pm 20%
2833864	V- 12- 24UC	Plug-in module, for mounting on PR1 and PR2, with varistor, input voltage: 12-24 V AC/DC \pm 20%
2833877	V- 48- 60UC	Plug-in module, for mounting on PR1 and PR2, with varistor, input voltage: 48-60 V AC/DC \pm 20%
2833880	V-120-230UC	Plug-in module, for mounting on PR1 and PR2, with varistor, input voltage: 120-230 V AC/DC \pm 20%

Marking

0819288	EML (15X6) R YE	Labels for thermal transfer printers, lettering field: 15 mm x 6 mm, 1 roll = 2500 labels, color: Yellow
---------	-----------------	--

Additional products

Item	Designation	Description
General		
2961257	REL-MR- 12DC/21-21	Pluggable miniature relays, with power contact, 2 PDT, input voltage 12 V DC
2961299	REL-MR- 12DC/21-21AU	Pluggable miniature relays, with multi-layer contact, 2 PDT, input voltage 12 V DC
2961309	REL-MR- 12DC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, input voltage 12 V DC
2961532	REL-MR- 12DC/21HC AU	Pluggable miniature relays, with power contact for high continuous current and additional hard gold plating, 1 PDT, input voltage 12 V DC
2961435	REL-MR- 24AC/21-21	Pluggable miniature relay, with power contact, 2 PDT, coil voltage 24 V AC
2987956	REL-MR- 24AC/21-21/MS	Plug-in miniature relay, with power contact, 2 PDTs, test button, mechanical switch position indicator, integrated LED, input voltage 24 V AC
2961464	REL-MR- 24AC/21-21AU	Pluggable miniature relay with power contact and additional hard gold plating, 2 PDT, coil voltage 24 V AC
2961406	REL-MR- 24AC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, input voltage 24 V AC
2961503	REL-MR- 24AC/21HC AU	Pluggable miniature relays, with power contact for high continuous current and additional hard gold plating, 1 PDT, input voltage 24 V AC
2987891	REL-MR- 24AC/21HC/MS	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, test button, mechanical switch position indicator, integrated LED, input voltage 24 V AC
2961341	REL-MR- 24DC/ 1IC	Pluggable miniature relays, with power contact for lamp loads and capacitive loads, 1 N/O contact, input voltage 24 V DC

2961192	REL-MR- 24DC/21-21	Pluggable miniature relays, with power contact, 2 PDT, input voltage 24 V DC
2987943	REL-MR- 24DC/21-21/MS	Plug-in miniature relay, with power contact, 2 PDTs, test button, mechanical switch position indicator, integrated LED and free-wheeling diode, input voltage 24 V DC
2961215	REL-MR- 24DC/21-21AU	Pluggable miniature relays, with multi-layer contact, 2 PDT, input voltage 24 V DC
2987985	REL-MR- 24DC/21-21AU/MS	Plug-in miniature relay, with multi-layer contact, 2 PDTs, test button, mechanical switch position indicator, integrated LED and free-wheeling diode, input voltage 24 V DC
2961312	REL-MR- 24DC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, input voltage 24 V DC
2961545	REL-MR- 24DC/21HC AU	Pluggable miniature relays, with power contact for high continuous current and additional hard gold plating, 1 PDT, input voltage 24 V DC
2987927	REL-MR- 24DC/21HC AU/MS	Pluggable miniature relays, with power contact for high continuous current, and with additional hard gold plating, 1 PDT, test button, mechanical switch position indicator, input voltage 24 V AC
2987888	REL-MR- 24DC/21HC/MS	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, test button, mechanical switch position indicator, integrated LED and free-wheeling diode, input voltage 24 V AC
2834834	REL-MR- 48DC/21-21	Plug-in miniature relay, with power contact, 2 PDT, input voltage 48 V DC
2834847	REL-MR- 48DC/21-21AU	Plug-in miniature relay, with multi-layer contact, 2 PDT, input voltage 48 V DC
2834821	REL-MR- 48DC/21HC	Plug-in miniature relay, with power contact for high continuous current, 1 PDT, 48 V DC
2961273	REL-MR- 60DC/21-21	Pluggable miniature relays, with power contact, 2 PDT, input voltage 60 V DC
2961286	REL-MR- 60DC/21-21AU	Pluggable miniature relays, with multi-layer contact, 2 PDT, input voltage 60 V DC
2961325	REL-MR- 60DC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, 60 V DC
2961202	REL-MR-110DC/21-21	Pluggable miniature relays, with power contact, 2 PDT, input voltage 110 V DC
2961228	REL-MR-110DC/21-21AU	Pluggable miniature relays, with multi-layer contact, 2 PDT, input voltage 110 V DC
2961338	REL-MR-110DC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, input voltage 110 V DC
2961561	REL-MR-110DC/21HC AU	Pluggable miniature relays, with power contact for high continuous current and additional hard gold plating, 1 PDT, input voltage 110 V DC
2961448	REL-MR-120AC/21-21	Pluggable miniature relay, with power contact, 2 PDT, coil voltage 120 V AC

2987969	REL-MR-120AC/21-21/MS	Plug-in miniature relay, with power contact, 2 PDTs, test button, mechanical switch position indicator, integrated LED, coil voltage 120 V AC
2961477	REL-MR-120AC/21-21AU	Pluggable miniature relay with power contact and additional hard gold plating, 2 PDT, coil voltage 120 V AC
2961419	REL-MR-120AC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, input voltage 120 V AC
2961516	REL-MR-120AC/21HC AU	Pluggable miniature relays, with power contact for high continuous current and additional hard gold plating, 1 PDT, input voltage 120 V AC
2987901	REL-MR-120AC/21HC/MS	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, test button, mechanical switch position indicator, integrated LED, input voltage 120 V AC
2961451	REL-MR-230AC/21-21	Pluggable miniature relay, with power contact, 2 PDT, coil voltage 230 V AC
2987972	REL-MR-230AC/21-21/MS	Plug-in miniature relay, with power contact, 2 PDTs, test button, mechanical switch position indicator, integrated LED, coil voltage 230 V AC
2961480	REL-MR-230AC/21-21AU	Pluggable miniature relay with power contact and additional hard gold plating, 2 PDT, coil voltage 230 V AC
2987998	REL-MR-230AC/21-21AU/MS	Plug-in miniature relay, with power contact and additional hard gold plating, 2 PDTs, test button, mechanical switch position indicator, integrated LED, coil voltage 230 V AC
2961422	REL-MR-230AC/21HC	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, input voltage 230 V AC
2961529	REL-MR-230AC/21HC AU	Pluggable miniature relays, with power contact for high continuous current and additional hard gold plating, 1 PDT, input voltage 230 V AC
2987930	REL-MR-230AC/21HC AU/MS	Pluggable miniature relays, with power contact for high continuous current, and with additional hard gold plating, 1 PDT, test button, mechanical switch position indicator, integrated LED, input voltage 230 V AC
2987914	REL-MR-230AC/21HC/MS	Pluggable miniature relays, with power contact for high continuous current, 1 PDT, test button, mechanical switch position indicator, integrated LED, input voltage 230 V AC

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;