

**FLK 20/2FLK14/EZ-DR/200/KONFEK**

Order No.: 2298438

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2298438>

Assembled circular cable, with one 20-pos. and two 14-pos. socket strips (for Emerson Delta V). The cable is suitable for coupling 8-channel modules. Length of cable: 2 m

**Commercial data**

EAN	4017918601911
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.1851 KG
Catalog page information	Page 196 (IF-2009)

**Product notes**

WEEE/RoHS-compliant since:  
03/09/2006



<http://>

[www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

**Technical data****General**

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 $\Omega$ /m

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions, control side	20
Number of connectors, control side	1
Number of positions, module side	14
Number of connectors, modul side	2
Fixed cable length	2 m
Single wire, cross section	0.14 mm <sup>2</sup>
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	7.6 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2010 Phoenix Contact  
Technical modifications reserved;