

C-UFB-24DC/E

Order No.: 2782313

The illustration shows version C-UFB- 5DC/E

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2782313>

Attachment plug with surge voltage coarse and fine protection, for coaxial signal interfaces with floating shield, signal voltage 24 V.
Connection: BNC female/male connector

Commercial data	
EAN	4017918069452
Pack	10 pcs.
Customs tariff	85363010
Weight/Piece	0.11369 KG
Catalog page information	Page 174 (TT-2009)

Product notes

WEEE/RoHS-compliant since:
08/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General	
Housing material	Aluminum
Color	black

Standards for air and creepage distances	VDE 0110-1
	IEC 60664-1: 1992-10
Total surge current (8/20) μ s	20 kA
Ambient temperature (operation)	-40 °C ... 80 °C
Mounting type	Connection-specific intermediate plugging
Design	Attachment plug
Degree of protection	IP20
Direction of action	Line-Shield/Earth Ground
Width	25.40 mm
Height	93.00 mm
Length	25.40 mm

Protective circuit

IEC category	C2
	C3
	D1
Arrester rated voltage U_c	30 V DC
Arrester rated voltage U_c (Core-Shield)	30 V DC
Nominal current I_N	185 mA (25°C)
Operating effective current I_c at U_c	$\leq 10 \mu$ A
Discharge current to PE at U_c	$\leq 2 \mu$ A
Nominal discharge surge current I_n (8/20) μ s (Core-Earth)	10 kA
Nominal discharge surge current I_n (8/20) μ s (Core-Shield)	10 kA
Total surge current (8/20) μ s	20 kA
Output voltage limitation at 1 kV/ μ s (Core-Earth) spike	≤ 500 V
Output voltage limitation at 1 kV/ μ s (Core-Shield) spike	≤ 160 V
Output voltage limitation at 1 kV/ μ s (Core-Earth) static	≤ 500 V
Output voltage limitation at 1 kV/ μ s (Core-Shield) static	≤ 42 V
Residual voltage at I_n , (conductor-ground)	≤ 50 V (10 cm cable)
Residual voltage at I_n , (conductor-shield)	≤ 43 V
Protection level U_p (Core-Earth)	≤ 450 V
Protection level U_p (Core-Shield)	≤ 35 V

Response time tA (Core-Earth)	≤ 100 ns
Response time tA (Core-GND)	≤ 500 ns
Input attenuation aE, asym.	1.7 dB (≤ 20 MHz)
Cut-off frequency fg (3 dB), asym. (shield) in 50 Ohm system	Typ. 170 MHz
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C2 (10 kV/5 kA)
	D1 (2.5 kA)

Connection data

Type of connection	BNC 50 Ω
Connection type IN	BNC socket
Connection type OUT	BNC plug

Connection, equipotential bonding

Type of connection	PVC litz wire
--------------------	---------------

Connection, protective circuit

Standards/regulations	IEC 61643-21
-----------------------	--------------

Certificates / Approvals




Certification


GOST

Diagrams/Drawings


Diagram



Dimensioned drawing



Circuit diagram



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;