

RAD-OUT-8D-REL

Order No.: 2867157



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867157>

Digital extension module with 8 digital outputs



Commercial data	
EAN	4017918929657
Pack	1 pcs.
Customs tariff	85371099
Weight/Piece	0.2009 KG
Catalog page information	Page 610 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
04/22/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Digital output

Output name	Relay output
Number of outputs	8

Maximum switching voltage	30 V AC/DC (EC Declaration of Conformity)
	30 V DC (With UL approval)
	250 V AC (With UL approval)
Limiting continuous current	0.5 A (EC Declaration of Conformity)

Supply

Range of supply voltages	9 V DC ... 30 V DC (via bus foot)
Typical current consumption	100 mA
Max. current consumption	160 mA

General data

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20
Mounting position	Any
Assembly instructions	on TS 35 profile rail acc. to EN 60715
Housing material	Polyamide PA non-reinforced
Width	22.5 mm
Height	114.5 mm
Depth	99 mm
Conformity	CE compliant
ATEX	Ex II 3 G EEx nL IIC
IECEX	Ex nL IIC
UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D

Connection data


Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M3

Certificates / Approvals

Certification Ex: CUL-EX LIS, IECEx, UL-EX LIS

Diagrams/Drawings

Block diagram



Approbationslogos (EX-Bereich)



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;