

PR2-BSC3/4X21

Order No.: 2833576

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2833576>

Relay socket PR2-B, for industrial relay REL-IR with 2 or 4 PDT, 1/3-level version, screw connections, connection facility for input/interference suppression modules, for mounting on NS 35/7.5

Commercial data

EAN	4017918933807
Pack	10 pcs.
Customs tariff	85366990
Weight/Piece	0.07315 KG
Catalog page information	Page 59 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
08/18/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section stranded min.	0.2 mm ²

Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
2 conductors with same cross section, solid max.	1.50 mm ²
2 conductors with same cross section, stranded max.	1.50 mm ²
2 conductors with same cross section, AWG max.	14
Type of connection	Screw connection
Stripping length	7 mm
Screw thread	M3

General data

Width	27 mm
Depth	78.5 mm
Height with retaining bracket	86 mm (EL2-P35)
Color	green
Ambient temperature (operation)	-25 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

Certificates / Approvals



Certification CSA, UL

Accessories

Item	Designation	Description
General		
2833592	EL2-P35	Relay retaining bracket, with eject function and integrated equipment marking area (8 x 25 mm), to suit relay socket PR2, for 35 mm high industrial relay
2833644	MP 2	Equipment marker, labeling surface 9 x 25 mm

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;